



The Physical Therapy Solution for the Veterinary Market

Chattanooga Group, the world's largest manufacturer of rehabilitation equipment for treating musculoskeletal, neurological, and soft tissue disorders, proudly brings their innovative products to the animal market. From the original Hydrocollator® HotPacs™ and heating units that Chattanooga Group pioneered 60 years ago, to the revolutionary advancements found in the Intelect® Vet system, no other company knows physical therapy and rehabilitation like Chattanooga Group.



Intelect® Vet is a revolutionary product for veterinarians who provide physical therapy to animals by offering four therapy modalities in one system:

- Electrical stimulation
- Ultrasound
- Combination stim and ultrasound
- Laser therapy

Intelect Vet is loaded with features designed to make the user interface simple to operate and treatment outcomes quickly achievable:

Clinical Protocols™ - give the most appropriate parameter set for a variety of clinical conditions, easily retrievable by choosing the specific body area to be treated. Rationale regarding waveforms and illustrations of correct electrode placement is also included.

User protocols - storage bank that houses over 100 user-defined treatment protocols

Anatomical library - full color graphic illustrations of the musculoskeletal system for both canine and equine, segmented by body area and clearly labeled

Patient documentation - capture patient information like electrode placements, pain scales and records of modalities used on provided patient data cards

Intelect Vet is designed to be fully functional in the clinic or to be used in an environment where mobility is a must. An optional battery module is available, allowing therapy to be performed away from outlets. With the optional carry bag, transport and storage of the unit and accessories are easy.



Electrotherapy

- Muscle strengthening
- Wound healing
- Edema
- Pain control
- Increase circulation
- Fracture healing





Laser Therapy

- Increase circulation
- Wound healing
- Tendonitis
- Pain control
- Decrease tendon and ligament inflammation









Ultrasound Therapy

- Increase Circulation
- Wound healing
- Increase soft tissue mobility
- Decrease tendon and ligament inflammation







Cold Therapy and Moist Heat Therapy

- Pain control
- Inflammation
- Decrease tendon and ligament inflammation







The therapeutic benefits of both moist heat therapy and cold therapy have been documented in the literature for years. This therapy can be easily applied to equines and canines with Chattanooga Group's moist heat hot packs and colpacs.

The original Hydrocollator® HotPacs™, which come in a variety of sizes, are designed to fit all body sizes, and contours. The packs are all natural, containing bentonite (a natural hydrocolloid filling) wrapped in a woven cotton blend. HotPacs provide up to 30 minutes of deep, soothing, moist heat relief.

Enclose the HotPac in the traditional terry knit weave Hydrocollator terry covers. These industrial use covers come in a variety of sizes to fit every HotPac. They stay securely in place with hook and loop closures.

Hydrocollator Heating Units, which house the HotPacs, are durable, stainless steel water tanks with fiberglass insulation throughout. They are thermostatically controlled to ensure the ideal therapeutic temperature for the HotPacs. Simply fill with water – no plumbing is required.

For cold therapy, Chattanooga Group's ColPaCs® are the benchmark. Choose either the blue vinyl or black polyurethane packs, available in a variety of sizes. Each are filled with a non-toxic silica gel that remains pliable, allowing easy application to virtually any area of the animal's body. The ColPaC delivers up to 30 minutes of soothing cold therapy.

HYDROCOLLATOR HEATING UNITS

M-2 37kg, (LxWxH) 84 x 67 x 41 cm
M-4 60kg, (LxWxH) 84 x 89 x 51 cm
SS-2 30kg, (LxWxH) 84 x 53 x 41 cm
SS 22kg, (LxWxH) 51 x 46 x 41 cm
E-1 7kg, (LxWxH) 41 x 33 x 20 cm
E-2 13kg, (LxWxH) 51 x 38 x 33 cm



Ordering Details

| REF PRODUCT DESCRIPTION 2756 Intelect Vet Combo (2 ch) 2843 Intelect Vet Combo (4 ch) Standard accessories include: 5cm² Ultrasound Applicator Patient Data Cards (5x), Patient Switch, Black and Red Carbon Electrodes, Lead Wires, Nylatex wraps, Ultrasound Gel, User Manual OPTIONAL ACCESSORIES 2766 Laser Module PRODUCT DESCRIPTION HYDROCOLLATOR® MOIST HEAT HOTPACS™ 23 cm x 39 cm (10" x 18") 25 cm x 61 cm (10" x 24") Oversize 38 cm x 61 cm (15" x 24") Neck Contour 61 cm (24" Long) Half Size 13 cm x 30 cm (5" x 12") Hand 17 cm x 32 cm (6.5" x 12.5") | |
|--|--------------------|
| 2756 Intelect Vet Combo (2 ch) 2843 Intelect Vet Combo (4 ch) Standard accessories include: 5cm² Ultrasound Applicator Patient Data Cards (5x), Patient Switch, Black and Red Carbon Electrodes, Lead Wires, Nylatex wraps, Ultrasound Gel, User Manual OPTIONAL ACCESSORIES 1014 HYDROCOLLATOR® MOIST HEAT HOTPACS™ 23 cm x 39 cm (10" x 18") 25 cm x 61 cm (10" x 24") Oversize 38 cm x 61 cm (15" x 24") Neck Contour 61 cm (24" Long) Half Size 13 cm x 30 cm (5" x 12") | |
| 2843 Intelect Vet Combo (4 ch) Standard accessories include: 5cm² Ultrasound Applicator Patient Data Cards (5x), Patient Switch, Black and Red Carbon Electrodes, Lead Wires, Nylatex wraps, Ultrasound Gel, User Manual OPTIONAL ACCESSORIES 1008 23 cm x 39 cm (10" x 18") 25 cm x 61 cm (10" x 24") Oversize 38 cm x 61 cm (15" x 24") Neck Contour 61 cm (24" Long) Half Size 13 cm x 30 cm (5" x 12") | |
| Standard accessories include: 5cm² Ultrasound Applicator Patient Data Cards (5x), Patient Switch, Black and Red Carbon Electrodes, Lead Wires, Nylatex wraps, Ultrasound Gel, User Manual OPTIONAL ACCESSORIES 1014 1010 25 cm x 61 cm (10" x 24") Oversize 38 cm x 61 cm (15" x 24") Neck Contour 61 cm (24" Long) Half Size 13 cm x 30 cm (5" x 12") | |
| Patient Data Cards (5x), Patient Switch, Black and Red Carbon Electrodes, Lead Wires, Nylatex wraps, Ultrasound Gel, User Manual OPTIONAL ACCESSORIES 1004 Oversize 38 cm x 61 cm (15" x 24") Neck Contour 61 cm (24" Long) Half Size 13 cm x 30 cm (5" x 12") | |
| Lead Wires, Nylatex wraps, Ultrasound Gel, User Manual OPTIONAL ACCESSORIES 1014 Neck Contour 61 cm (24" Long) Half Size 13 cm x 30 cm (5" x 12") | |
| OPTIONAL ACCESSORIES 1014 Half Size 13 cm x 30 cm (5" x 12") | |
| 1) / 6 | |
| | |
| 2767 Battery module 1006 Standard 25 cm x 30 cm (10" x 12") | |
| 27333 1 cm2 Ultrasound Applicator TERRY COVERS | |
| 27334 2 cm2 Ultrasound Applicator 1118 Standard 48 cm x 69 cm (19" x 27") | |
| | |
| 27/469 Intelect Carry Bag | |
| 27508 Operator Pomoto (ch. 1/2) | |
| 27308 Operator Remote (ch 1/2) 27079 Operator Remote (ch 3/4) 1132 Hand Contour Dual Pocket Terry Cover 58 cm x 36 cm (23" x 14") | |
| 2775 Therapy System Cart 1102 Standard Size Foam-Filled 48 cm x 69 cm (19" | 27"\ |
| 2785 Vacuum Electrode Module 1124 Oversize Foam-Filled 61 cm x 91 cm (24" x 36" | |
| 2774 Vacuum Module w/ Therapy System Cart 1120 Neck Contour Foam-Filled 64 cm x 41cm (25" x | |
| 27799 670nm LED Diode 10mW 1108 Standard Foam-Filled Pocket 43 cm x 69 cm (17 | |
| office of the billion | |
| OTO 10 OTO 1 DE 1 100 W | x 30) |
| office to the production of th | |
| 27041 950 I man Disala 200W | |
| OZOOF OOO I D. I SOO W | |
| 27010 0 D. 1 Cl. 1 A 1: 1 200 M/T - 1 | |
| 5 v 850nm 50mW lacere 4 v 670nm 10mW IED 2500 M-4 Mobile Hydrocolidiol 220 v Ollil (2502 12 | |
| 278.1. 9 Diode Cluster Applicator, 540mW Total: 2307 55-2 Mobile Hydrocollator 220 V Unit (2302-120 | |
| 5 x 850nm 100mW Lasers, 4 x 670nm 10mW LED 2207 55 Stationary Hydrocollator 220 V Unit (2202 12 | |
| 27812 9 Diode Cluster Applicator, 1040mW Total: 2107 E-1 Stationary Hydrocollator 220 V Unit (2102 12 | |
| 5 x 850nm 200mW Lasers, 4 x 670nm 10mW LED 2806 E-2 Stationary Hydrocollator 220 V Unit (2802 12 |) V Unit) |
| 27813 13 Diode Cluster Applicator, 265mW Total: | |
| 3 x 850nm 50mW Lasers, 7 x 670nm 10mW LED, HEATING UNIT TECHNICAL SPECIFICATIONS | |
| 3 x 950nm 15mWLED Mains Power: 110~240 V 50/60 Hz | |
| 27814 13 Diode Cluster Applicator, 415mW Total: 3 x 850nm 100mW Lasers, 7 x 670nm 10mW LED, Power Consumption: 1000 W Electricial Safety Class: Class 1, Type B | |
| 3 x 850nm 100mW Lasers, 7 x 670nm 10mW LED, 3 x 950nm 15mW LED Electricial Safety Class: Class 1, Type B Safety Tests: EN 60601-1 | |
| 27816 13 Diode Cluster Applicator, 715mW Total: | |
| 3 x 850nm 200mW Lasers, 7 x 670nm 10mW LED, BILLE VINYL COLPACS | |
| 3 x 950nm 15mW LED 1512 Oversize 28 cm x 53 cm (11" x 21") | |
| | |
| 27815 19 Diode Cluster Applicator, 325mW Total: 1500 Standard Size 28 cm x 36 cm (11 x 21) | |
| 27815 19 Diode Cluster Applicator, 325mW Total: 1512 Oversize 28 cm x 35 cm (11 x 21) no Lasers, 6 x 670nm 10mW LED, 1500 Standard Size 28 cm x 36 cm (11" x 14") | |
| 27815 19 Diode Cluster Applicator, 325mW Total: 1500 Standard Size 28 cm x 36 cm (11" x 14") no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 1506 Half Size 19 cm x 28 cm (7.5" x 11") | |
| 27815 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 27809 33 Diode Cluster Applicator, 565mW Total: 1500 Standard Size 28 cm x 36 cm (11" x 14") Half Size 19 cm x 28 cm (7.5" x 11") Neck contour 58 cm (23" Long) | |
| 27815 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 27809 33 Diode Cluster Applicator, 565mW Total: 1500 Standard Size 28 cm x 36 cm (11" x 14") Half Size 19 cm x 28 cm (7.5" x 11") Neck contour 58 cm (23" Long) | |
| 27815 19 Diode Cluster Applicator, 325mW Total: | |
| 27815 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 27809 33 Diode Cluster Applicator, 565mW Total: no Lasers, 12 x 670nm 10mW LED, 13 x 880nm 25mW LED, 8 x 950nm 15mW LED 27802 33 Diode Cluster Applicator, 690mW Total: 5 x 850nm 50mW Lasers, 12 x 670nm 10mW LED, 1504 Standard Size 28 cm x 36 cm (11" x 14") Half Size 19 cm x 28 cm (7.5" x 11") Neck contour 58 cm (23" Long) 8 cm x 28 cm (3" x 11") Quarter Size 14 cm x 19 cm (5.5" x 7.5") 8 LACK POLYURETHANE COLPACS | |
| 27815 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 1500 Standard Size 28 cm x 36 cm (11" x 14") 27809 33 Diode Cluster Applicator, 565mW Total: no Lasers, 12 x 670nm 10mW LED, 13 x 880nm 25mW LED, 8 x 950nm 15mW LED 1508 Neck contour 58 cm (23" Long) 27802 33 Diode Cluster Applicator, 690mW Total: 5 x 850nm 50mW Lasers, 12 x 670nm 10mW LED, 8 x 950nm 15mW LED 1504 Quarter Size 14 cm x 19 cm (5.5" x 7.5") BLACK POLYURETHANE COLPACS Neck Contour 53 cm Long (21" Long) Neck Contour 53 cm Long (21" Long) | |
| 19 Diode Cluster Applicator, 325mW Total: 1500 | |
| 27815 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 1500 Standard Size 28 cm x 36 cm (11" x 14") 27809 33 Diode Cluster Applicator, 565mW Total: no Lasers, 12 x 670nm 10mW LED, 13 x 880nm 25mW LED, 8 x 950nm 15mW LED 1508 Neck contour 58 cm (23" Long) 27802 33 Diode Cluster Applicator, 690mW Total: 5 x 850nm 50mW Lasers, 12 x 670nm 10mW LED, 8 x 950nm 15mW LED 1504 Quarter Size 14 cm x 19 cm (5.5" x 7.5") 27807 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 10mW Lasers, 12 x 670nm 10mW LED, 5 x 850nm 10mW Lasers, 12 x 670nm 10mW LED, 1556 1554 Neck Contour 53 cm Long (21" Long) 27807 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 10mW Lasers, 12 x 670nm 10mW LED, 1550 1556 Oversize 32 cm x 47 cm (12.5" x 18.5") 27807 35 Link x 14") 1500 1554 Neck Contour 53 cm Long (21" Long) 27807 37 Diode Cluster Applicator, 940mW Total: 5 x 850nm 10mW Lasers, 12 x 670nm 10mW LED, 1550 1550 Standard Size 25 cm x 34 cm (10" x 13.5") | |
| 27815 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 1500 Standard Size 28 cm x 36 cm (11" x 14") 27809 33 Diode Cluster Applicator, 565mW Total: no Lasers, 12 x 670nm 10mW LED, 13 x 880nm 25mW LED, 8 x 950nm 15mW LED 1508 Neck contour 58 cm (23" Long) 27802 33 Diode Cluster Applicator, 690mW Total: 5 x 850nm 50mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 1504 Quarter Size 14 cm x 19 cm (5.5" x 7.5") 27807 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 950nm 15mW LED 1554 Neck Contour 53 cm Long (21" Long) 27807 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 950nm 15mW LED 1556 Oversize 32 cm x 47 cm (12.5" x 18.5") 27807 38 S80nm 25mW LED, 8 x 950nm 15mW LED, 9 x 950nm 15 | |
| 19 Diode Cluster Applicator, 325mW Total: | v 39 cm |
| 19 Diode Cluster Applicator, 325mW Total: 1500 Standard Size 28 cm x 36 cm (11" x 14") 1500 Standard Size 28 cm x 36 cm (11" x 14") 1500 Half Size 19 cm x 28 cm (7.5" x 11") 1506 Half Size 19 cm x 28 cm (7.5" x 11") 1508 Neck contour 58 cm (23" Long) 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 1500 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 8 cm x 28 cm (3" x 11") 1500 1500 8 cm x 28 cm (3" x 11") 1500 1500 8 cm x 28 cm (3" x 11") 1500 1500 8 cm x 28 cm (3" x 11") 1500 | |
| 19 Diode Cluster Applicator, 325mW Total: 1500 Standard Size 28 cm x 36 cm (11" x 14") | x 39 cm |
| 19 Diode Cluster Applicator, 325mW Total: | x 39 cm x 51 cm |
| 19 Diode Cluster Applicator, 325mW Total: 1500 Standard Size 28 cm x 36 cm (11" x 14") | x 39 cm x 51 cm |
| 19 Diode Cluster Applicator, 325mW Total: | x 39 cm x 51 cm |
| 27815 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 1500 13 x 880nm 25mW LED, 8 x 950nm 15mW LED 1504 27802 33 Diode Cluster Applicator, 565mW Total: 5 x 850nm 50mW LED, 8 x 950nm 15mW LED 27807 33 Diode Cluster Applicator, 690mW Total: 5 x 850nm 50mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 940mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 940mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm | x 39 cm x 51 cm |
| 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 1500 | x 39 cm x 51 cm |
| 27815 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 1506 | x 39 cm x 51 cm |
| 27815 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 1504 27807 33 Diode Cluster Applicator, 565mW Total: no Lasers, 12 x 670nm 10mW LED, 1504 | x 39 cm x 51 cm |
| 27815 19 Diode Cluster Applicator, 325mW Total: no lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 27809 33 Diode Cluster Applicator, 565mW Total: no lasers, 12 x 670nm 10mW LED, 13 x 880nm 25mW LED, 8 x 950nm 15mW LED 27802 33 Diode Cluster Applicator, 690mW Total: 5 x 850nm 50mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27807 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 50mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 3104 CC-2 220 V Unit (3102 110 V Unit) 74kg, (LxWxH) 84 x 65 cc. 220 V Unit) (3102 110 V Unit) 74kg, (LxWxH) 84 x 65 cc. 220 V Unit) (3102 110 V Unit) 74kg, (LxWxH) 84 x 65 cc. 220 V Unit) (3102 110 V Unit) 74kg, (LxWxH) 84 x 65 cc. 220 V Unit) (3102 110 V Unit) 74kg, (LxWxH) 84 x 65 cc. 220 V Unit) (3102 110 V Unit) 74kg, (LxWxH) 84 x | x 39 cm x 51 cm |
| 27815 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 27809 33 Diode Cluster Applicator, 565mW Total: no Lasers, 12 x 670nm 10mW LED, 13 x 880nm 25mW LED, 8 x 950nm 15mW LED 27802 33 Diode Cluster Applicator, 690mW Total: 5 x 850nm 50mW LED, 8 x 950nm 15mW LED 27807 33 Diode Cluster Applicator, 690mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27807 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 30 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 31 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator, 940mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator, 940mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator, 940mW Total: 5 x 850nm 25mW LED, 8 x 950nm 15mW LED 27808 32 Diode Cluster Applicator | x 39 cm x 51 cm |
| 27815 | x 39 cm x 51 cm |
| 27815 19 Diode Cluster Applicator, 325 mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 27809 33 Diode Cluster Applicator, 565mW Total: no Lasers, 12 x 670nm 10mW LED, 13 x 880nm 25mW LED, 8 x 950nm 15mW LED 27802 33 Diode Cluster Applicator, 690mW Total: 5 x 850nm 50mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27807 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 740mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 80nm 20mW LED, 8 x 80nm 20m | x 39 cm x 51 cm |
| 27815 19 Diode Cluster Applicator, 325mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 1500 | x 39 cm x 51 cm |
| 27815 19 Diode Cluster Applicator, 325 mW Total: no Lasers, 6 x 670nm 10mW LED, 7 x 880nm 25mW LED, 6 x 950nm 15mW LED 27809 33 Diode Cluster Applicator, 565mW Total: no Lasers, 12 x 670nm 10mW LED, 13 x 880nm 25mW LED, 8 x 950nm 15mW LED 27802 33 Diode Cluster Applicator, 690mW Total: 5 x 850nm 50mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27807 33 Diode Cluster Applicator, 940mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 740mW Total: 5 x 850nm 100mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 880nm 25mW LED, 8 x 950nm 15mW LED 27808 33 Diode Cluster Applicator, 1440mW Total: 5 x 850nm 200mW Lasers, 12 x 670nm 10mW LED, 8 x 80nm 20mW LED, 8 x 80nm 20m | x 39 cm x 51 cm |

















| Distributed by: | | | |
|-----------------|--|--|--|
| | | | |
| | | | |
| | | | |
| | | | |